

Designed and built for size, throughput, precision and repeatability.

The **Stratasys F900**® is one of the most precise and powerful **FDM**® systems available. With the largest build size of any Stratasys FDM system, the Stratasys F900 is designed to handle the most demanding manufacturing needs. The accuracy, repeatability and predictability are unmatched, and the control software leverages the system's hardware to deliver superior throughput and reliability.

The Stratasys F900 uses Stratasys Preferred and Validated thermoplastics to build robust production parts, jigs, fixtures, factory tooling and functional prototypes. Large parts are printed fast with slice heights 0.020 inches (0.508 mm) to help meet production demands with ease. OpenAM™ software enables the use of third-party open materials and lets users alter machine print parameters to optimize material capabilities and print results.

The F900 offers an internal camera for easier job monitoring and a streamlined workflow enabled by GrabCAD Print software and MTConnect readiness. Data security, including U.S. Department of Defense STIG compliance, is provided by Stratasys ProtectAM™ technology. Standard certifications are included and reduce workload to qualify 3D printers for a production floor.

System Specifications

| | |
|-----------------------------|---|
| Build Envelope (XYZ) | 914.4 x 609.6 x 914.4 mm (36 x 24 x 36 in.) Platen supports two build zones for either a small or large build sheet |
| Material Delivery | Two model material canisters 1,508 cc (92 in. ³); Two support material canisters 1,508 cc (92 in. ³) Auto changeover between canisters |

Other Specifications

| | |
|--------------------------------|--|
| System Size and Weight | 2,772 x 1,683 x 2,027 mm (109.1 x 66.3 x 79.8 in.); 2,869 kg (6,325 lbs.) With Manufacturing Light Tower: 2,772 x 1,683 x 2,281 mm (109.1 x 66.3 x 89.8 in.) |
| Achievable Accuracy | Parts are produced within an accuracy of +/- .089 mm or +/- .0015 mm per mm whichever is greater (+/- .0035 in. or +/- .0015 in. per in. whichever is greater). + Z part accuracy includes an additional tolerance of -0.000/+ slice height. Note: Accuracy is geometry-dependent. Achievable accuracy specification derived from statistical data at 95% dimensional yield. See Fortus 900mc accuracy white paper for more information. |
| Network Communication | Wired: TCP/IPV6 protocols, 10/100 base T connection, Ethernet protocol |
| Operator Attendance | Limited attendance for job start and stop required |
| Operating Environment | Maximum room temperature of 29 °C (85 °F). Maximum room humidity of 80% |
| Power Requirements | 230 VAC (three phase) 50/60Hz, Voltage fluctuation +/- Current 40A |
| Additional Requirements | Compressed Air Required 90-120 psi with a minimum flow of 20 CFM |
| Regulatory Compliance | CE, cTUVus, RCM, EAC, FCC Part B |
| Software | All Fortus systems include Insight and Control Center™ job processing and management software. Compatible with GrabCAD Print and GrabCAD Streamline Pro™ for use with job reports, scheduling and remote monitoring. U.S. government agency STIG compliance via Stratasys ProtectAM technology is powered by Red Hat® Enterprise Linux® software. GrabCAD Print Pro is available with a paid subscription and OpenAM software is available with the purchase of an OpenAM license. |
| Operating System | Insight: Microsoft Windows 11, Microsoft Windows 10, or Microsoft Windows Server 2012 R2 GrabCAD Print, GrabCAD Print Pro, and OpenAM: Windows 10 and newer, Windows Server 2016 and newer. Only 64-bit versions of Windows are supported. |

Material Options

Stratasys Preferred Materials

| Material | Layer Thickness | | | | | Support Structure | Available Colors |
|-------------------|--------------------------|-------------------------|-------------------------|-------------------------|--------------------------|-----------------------|---|
| | 0.020 inch (0.508 mm) | 0.013 in. (0.330 mm) | 0.010 in. (0.254 mm) | 0.007 in. (0.178 mm) | 0.005 inch (0.127 mm) | | |
| ASA | ● | ● | ● | ● | ● | Soluble | <ul style="list-style-type: none"> ■ Black ■ Dark Gray ■ Light Gray □ White ■ Ivory ■ Dark Blue ■ Green ■ Yellow ■ Orange ■ Red |
| ABS-M30™ | ○ | ● | ● | ● | ○ | Soluble | <ul style="list-style-type: none"> ■ Ivory □ White ■ Black ■ Red ■ Blue ■ Dark Gray |
| ABS-M30i™ | ○ | ● | ● | ● | ○ | Soluble | <ul style="list-style-type: none"> ■ Ivory |
| ABS-ESD7™ | ○ | ○ | ● | ● | ○ | Soluble | <ul style="list-style-type: none"> ■ Black |
| Antero™ 800NA | ○ | ○ | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Natural |
| Antero™ 840CN03 | ○ | ○ | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Natural |
| PC-ABS | ○ | ● | ● | ● | ○ | Soluble | <ul style="list-style-type: none"> ■ Black |
| PC-ISO™ | ○ | ● | ● | ● | ○ | Breakaway | <ul style="list-style-type: none"> ■ Translucent Natural □ White |
| PC | ○ | ● | ● | ● | ○ | Breakaway, Soluble | <ul style="list-style-type: none"> □ White |
| ULTEM™ 9085 resin | ● | ● | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Tan ■ Black |
| ULTEM™ 1010 resin | ● | ● | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Natural |
| PPSF | ○ | ○ | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Tan |
| FDM® Nylon 12 | ○ | ● | ● | ● | ○ | Soluble | <ul style="list-style-type: none"> ■ Black |
| FDM® Nylon 6 | ○ | ● | ● | ○ | ○ | Soluble | <ul style="list-style-type: none"> ■ Black |
| FDM® Nylon 12CF | ● | ○ | ● | ○ | ○ | Soluble | <ul style="list-style-type: none"> ■ Black |
| ST-130™ | ○ | ● | ○ | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Natural |

Material Options

Stratasys Validated Materials

| Material | Layer Thickness | | | | Support Structure | Available Colors |
|----------------------------|-------------------------|-------------------------|-------------------------|--------------------------|--------------------|---|
| | 0.013 in. (0.330 mm) | 0.010 in. (0.254 mm) | 0.007 in. (0.178 mm) | 0.005 inch (0.127 mm) | | |
| FDM HIPS | ○ | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Light Gray |
| Kimya PC-FR | ○ | ● | ○ | ○ | Soluble | <ul style="list-style-type: none"> ■ Light Gray |
| ULTEM® 9085 Resin (colors) | ● | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Red |
| | ○ | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Jana White |
| | ○ | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Dream Gray |
| | ○ | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> □ White 7362 |
| | ○ | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Gunship Gray |
| | ● | ● | ○ | ○ | Breakaway | <ul style="list-style-type: none"> ■ Aircraft Gray |
| PC (colors) | ○ | ● | ○ | ○ | Soluble | <ul style="list-style-type: none"> ■ Red |
| PC-ABS (colors) | ○ | ● | ○ | ○ | Soluble | <ul style="list-style-type: none"> ■ Red |
| VICTREX AM™ 200 | ○ | ● | ○ | ○ | Breakaway, Soluble | <ul style="list-style-type: none"> ■ Natural |
| PC-ESD | ○ | ● | ○ | ○ | Soluble | <ul style="list-style-type: none"> ■ Black |



stratasys.com
ISO 9001:2015
Certified

Stratasys Headquarters
7665 Commerce Way,
Eden Prairie, MN 55344
+1 800 801 6491 (US Toll Free)
+1 952 937-3000 (Intl)
+1 952 937-0070 (Fax)

1 Holtzman St., Science Park,
PO Box 2496
Rehovot 76124, Israel
+972 74 745 4000
+972 74 745 5000 (Fax)

PRODUCT SPEC SHEET FDM

© 2024 Stratasys. All rights reserved. Stratasys, FDM, F900 and Fortus are registered trademarks of Stratasys Inc. GrabCAD Print, GrabCAD Print Pro, GrabCAD Streamline Pro, OpenAM, ProtectAM, Insight, ABS-M30, ABS-M30i, ABS-ESD7, PC-ISO, FDM Nylon 6, FDM Nylon 12, FDM Nylon 12CF, Antero 800NA, Antero 840CN03 and ST-130 are trademarks of Stratasys, Inc. 9085, 1010 and ULTEM™ are trademarks of SABIC, its affiliates or subsidiaries. VICTREX AM™ 200 is a trademark of Victrex Manufacturing Ltd. Red Hat is a registered trademark of Red Hat, Inc. in the United States and other countries. All other trademarks are the property of their respective owners, and Stratasys assumes no responsibility with regard to the selection, performance, or use of these non-Stratasys products. Product specifications subject to change without notice. PSS_FDM_StratasysF900_0924a